

AGILA TWIN

2977POO075P50

EAN 4031582439427



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	102 mm
Overall width	71 mm
Overall weight	0.527 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	75 mm
Tread width	22 mm
Body width	25 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	31.3 mm
Swivel radius	99 mm
Swivel interference	198 mm

FITTING

Fitting type	Rectangular plate
Plate length	77 mm
Plate width	67 mm
Plate hole length (Minimum)	46.5 mm
Plate hole length (Maximum)	51.5 mm
Plate hole width (Minimum)	56 mm
Plate hole width (Maximum)	61.5 mm
Plate hole diameter	8.5 mm

PRODUCT INFORMATION

AGILA TWIN

2977POO075P50

EAN 4031582439427



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

