

# LUMINA

A525POI050S70-10X15

EAN 4031582455915



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Lumina
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	56 mm
Overall width	54 mm
Overall weight	0.056 kg

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Tread width	7 mm
Hardness of tread (D)	65 Shore D

## HOUSING

Material fork	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Swivel radius	62 mm
Swivel interference	124 mm
Thread diameter	10 mm

## FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	15 mm

PRODUCT INFORMATION

# LUMINA

A525POI050S70-10X15

EAN 4031582455915



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

