

OMIKRON TWIN

9950STP500P68 RADBREITE 100

EAN 4031582428964



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Omikron twin
Housing type	Swivel castor
Load capacity at 3 km/h	10000 kg
Load capacity at 4 km/h	10000 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	610 mm
Overall weight	130.875 kg

WHEEL

Body material	Sheet steel, heavy
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	500 mm
Tread width	100 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	130 mm
Swivel radius	380 mm
Swivel interference	760 mm

FITTING

Fitting type	Rectangular plate
Plate length	270 mm
Plate width	250 mm
Plate hole length (Maximum)	230 mm
Plate hole width (Maximum)	210 mm
Plate hole diameter	17 mm

OMIKRON TWIN

9950STP500P68 RADBREITE 100

EAN 4031582428964



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

