

COMPACTA

1530PJO040P41

EAN 4031582425376



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product name	Compacta
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	20 kg
Load capacity Static	40 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	51 mm
Overall weight	0.068 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Axle	Riveted
Threadguards	Without threadguard
Diameter	40 mm
Tread width	23 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Steel sheet, light
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	One ball race
Offset	19 mm
Swivel radius	39 mm
Swivel interference	78 mm

FITTING

Fitting type	Square plate
Plate length	37 mm
Plate width	37 mm
Plate hole length (Maximum)	30 mm
Plate hole width (Maximum)	30 mm