

AGILA

2475YGO050B10-11X31

EAN 4031582356366



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	110.23 lb
Electric conductive	✓
Load capacity Static	220.46 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.83 in
Overall weight	0.41 lb

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Thermoplastic rubber, electric-conductive
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.75 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	0.94 in

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in

AGILA

2475YGO050B10-11X31

EAN 4031582356366



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

