

# STYLEA

5920UAP100L51-11 DOM41

EAN 4031582370645



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Stylea
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	3.98 in
Overall width	2.95 in
Overall weight	0.31 lb

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Axle	Riveted
Threadguards	With threadguard
Diameter	3.94 in
Tread width	0.79 in

## HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	3.46 in
Swivel interference	6.93 in
Dome diameter	1.61 in

## FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.43 in

PRODUCT INFORMATION

# STYLEA

5920UAP100L51-11 DOM41

EAN 4031582370645



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

