

AGILA TWIN

2970PJO050P40

EAN 4031582302691



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Agila twin
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Electric Conductive	No
Stainless	No
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	69 mm
Overall width	53 mm
Overall weight	0.22 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	25 mm
Swivel radius	53 mm
Swivel interference	106 mm
Dome diameter	53 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	19 mm
Body width	19 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Square plate
Plate length	60 mm
Plate width	60 mm
Plate hole length (Minimum)	38 mm
Plate hole length (Maximum)	48 mm
Plate hole width (Minimum)	38 mm
Plate hole width (Maximum)	48 mm
Plate hole diameter	6.3 mm

AGILA TWIN

2970PJO050P40

EAN 4031582302691

Order number 00030308

Product Drawings



BETTER MOBILITY. BETTER LIFE.

