

COMPACTA

2198UOI045P60-67x24

EAN 4031582030075



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Compacta
Type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall Height	48.5 mm
Overall width	20 mm
Overall weight	0.06 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Angular
Swivel Bearing	Fixed housing
Housing Color	Blue passivated
Dome diameter	20 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	45 mm
Tread width	18 mm
Body width	18 mm
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	67 mm
Plate width	24 mm
Plate hole length (Maximum)	54 mm
Plate hole width (Maximum)	54 mm
Plate hole diameter	5.3 mm

COMPACTA

2198UOI045P60-67x24

EAN 4031582030075

Order number 00021141

Product Drawings



BETTER MOBILITY. BETTER LIFE.

