

ALPHA STAINLESS

8477BOG100P30-13

EAN 4031582480429



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha stainless |
| Type | Swivel castor with total lock |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 125 kg |
| Stainless | ✓ |
| Load capacity Static | 250 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 280 °C |
| Overall height | 128 mm |
| Overall weight | 0.719 kg |

WHEEL

| | |
|-----------------------|-----------------------------------|
| Body material | Plastic thermoset, heat-resistant |
| Tread material | Identical with wheel body |
| Bearing | Dry bearing bush |
| Axle | Screwed with nut |
| Diameter | 100 mm |
| Tread width | 35 mm |
| Hardness of tread (D) | 85 Shore D |

HOUSING

| | |
|---------------------|------------------------|
| Material fork | Stainless steel, heavy |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 41 mm |
| Swivel radius | 91 mm |
| Swivel interference | 182 mm |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 13 mm |