



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	ICS
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	166 mm
Overall width	52 mm
Overall weight	0.657 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing, sealed
Wheel color	Silver grey (RAL7001)
Threadguards	Integrated threadguard
Diameter	125 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Slim
Swivel bearing	Stem, swiveling
Colour	Silver grey (RAL7001)
Offset	37 mm
Swivel radius	99.5 mm
Swivel interference	199 mm
Dome diameter	52 mm

## FITTING

Fitting type	Rectangular plate
Plate length	95 mm
Plate width	70 mm
Plate hole length (Maximum)	50 mm
Plate hole width (Maximum)	75 mm
Plate hole diameter	11 mm



IF  
Design  
Award

## TECHNICAL DRAWINGS

