

STYLEA

5920UOI065B10-11X20 DOM32

EAN 4031582310870
Order number 00078717



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel castor
Load capacity at 3 km/h	50 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	72 mm
Overall width	46 mm
Overall weight	0.124 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	65 mm
Tread width	7 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	53 mm
Swivel interference	106 mm
Dome diameter	32 mm

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm

PRODUCT INFORMATION

STYLEA

5920UOI065B10-11X20 DOM32

EAN 4031582310870
Order number 00078717



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

