

LUMINA

6A23YOI050B10-11X20/10 RK. SCHWARZ

EAN 4031582340556
Order number 00073825



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor with intermittend brake
Electric conductive	✓
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	59 mm
Overall width	55 mm
Overall weight	0.128 kg

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Tread width	8 mm
Body width	8 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Zinc-die-casting / Aluminium
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Swivel radius	51 mm
Swivel interference	102 mm

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm

PRODUCT INFORMATION

LUMINA

6A23YOI050B10-11X20/10 RK. SCHWARZ

EAN 4031582340556
Order number 00073825



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

