

AGILA CARE

2474XSP150R36-32S30 D 4XM6

EAN 4031582358179
Order number 00061545



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Agila care
Type	Swivel castor with central, total or directional lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	✓
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	7.4 in
Overall width	2.36 in
Overall weight	2.46 lb

WHEEL

Body material	Polyamide, electric conductive
Tread material	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	5.91 in
Tread width	1.26 in
Body width	1.26 in
Hardness of tread (A)	91 Shore A
Hardness of tread (D)	40 Shore D

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Color	Blue passivated
Offset	1.77 in
Swivel radius	4.72 in
Swivel interference	9.45 in
Dome diameter	2.36 in

FITTING

Fitting type	Stem with cam hole for profile bars, short version
Bolt diameter	1.26 in
Bolt length	2.01 in
Bolt thread position	0.28 in
Bolt mounting holes quantity	4

PRODUCT INFORMATION

AGILA CARE

2474XSP150R36-32S30 D 4XM6

EAN 4031582358179
Order number 00061545



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

