

# AGILA

2477PJP075R07-Ø19-21,5

EAN 4031582326659  
Order number 00061564



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance ●●●○○

Movement noise ●●●○○

Attrition ●●●○○

Corrosion resistance ●●●○○

## CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	60 kg
Load capacity Static	120 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	103 mm
Overall weight	0.425 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	24 mm
Swivel radius	80 mm
Swivel interference	160 mm

## FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	19 mm
Expander fitting (Maximum)	21.5 mm
Hint	Please indicate required tube innerdiameter when ordering.

# AGILA

2477PJP075R07-Ø19-21,5

EAN 4031582326659  
Order number 00061564



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

