

# KAPPA LOAD

9652ITP250P63 FLAT KICK PEDAL

EAN 4031582445305



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Kappa load
Type	Swivel castor with total lock, head end of castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2204.62 lb
Load capacity Static	4409.24 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	12.01 in

## WHEEL

Body material	Aluminum
	flat
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	9.84 in
Tread width	2.17 in
Hardness of tread (A)	92 Shore A

## HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	2.4 in
Swivel radius	7.36 in
Swivel interference	14.72 in
	✓

## FITTING

Fitting type	Rectangular plate
Plate length	5.31 in
Plate width	4.33 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

# KAPPA LOAD

9652ITP250P63 FLAT KICK PEDAL

EAN 4031582445305



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

