

COMPACTA

1530POO050P41

EAN 4031582429237



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product name	Compacta
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	69 mm
Overall weight	0.18 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Hardness of tread (A)	95 Shore A

HOUSING

Material fork	Steel sheet, light
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	One ball race
Offset	20 mm
Swivel radius	45 mm
Swivel interference	90 mm

FITTING

Fitting type	Square plate
Plate length	40 mm
Plate width	40 mm
Plate hole length (Maximum)	30 mm
Plate hole width (Maximum)	30 mm
Plate hole diameter	4.5 mm