

# AGILA TWIN

2970PJP050P30-11 TNL

EAN 4031582333541



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	70 mm
Overall weight	0.54 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	50 mm
Tread width	18 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	25 mm
Swivel radius	50 mm
Swivel interference	100 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	10 mm

# AGILA TWIN

2970PJP050P30-11 TNL

EAN 4031582333541



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

