

NOVATECH

FTP 250X50-Ø25 HL60

EAN 4031582319385
Order number 00800995



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	250 mm
Tread width	50 mm
Axle hole diameter	25 mm
Hub length	60 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1440 kg
Load capacity at 6 km/h	1200 kg
Load capacity Static	2400 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	6.5 kg

NOVATECH

FTP 250X50-Ø25 HL60

EAN 4031582319385
Order number 00800995



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

