

# KAPPA

9688FTP250P65

EAN 4031582316322



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Kappa
Type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	4497.42 lb
Load capacity at 3.7 mph	3747.85 lb
Load capacity Static	8994.85 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	12.01 in
Overall weight	41.53 lb

## WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	9.84 in
Tread width	3.15 in
Hardness of tread (A)	92 Shore A

## HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
	✓

## FITTING

Fitting type	Rectangular plate
Plate length	7.87 in
Plate width	6.3 in
Plate hole length (Maximum)	6.3 in
Plate hole width (Maximum)	4.72 in
Plate hole diameter	0.59 in

# KAPPA

9688FTP250P65

EAN 4031582316322



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

