

AGILA TWIN

2976UAE075P54

EAN 4031582302882



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---|
| Product name | Agila twin |
| Housing type | Swivel castor with central , total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 220.46 lb |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 4.06 in |
| Overall weight | 1.48 lb |

WHEEL

| | |
|-----------------------|------------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Cone ball bearing, stainless |
| Diameter | 2.95 in |
| Tread width | 0.98 in |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|---------------------|
| Material | Steel sheet, medium |
| Fork shape | Twin wheel housing |
| Swivel bearing | Two ball races |
| Offset | 1.1 in |
| Swivel radius | 2.58 in |
| Swivel interference | 5.16 in |

FITTING

| | |
|-----------------------------|---------------------------------------|
| Fitting type | Rectangular plate with brake elements |
| Plate length | 2.76 in |
| Plate width | 2.17 in |
| Plate hole length (Minimum) | 2.01 in |
| Plate hole length (Maximum) | 2.24 in |
| Plate hole width (Maximum) | 1.61 in |
| Plate hole diameter | 0.22 in |

AGILA TWIN

2976UAE075P54

EAN 4031582302882



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

