

# AGILA TWIN

2970UOO050P30-11

EAN 4031582302769  
Order number 00030048



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall height	69 mm
Overall width	53 mm
Overall weight	0.184 kg

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Wheel color	Slate grey (RAL7015)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	20 mm
Body width	20 mm
Hardness of tread (D)	75 Shore D

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	25 mm
Swivel radius	53 mm
Swivel interference	106 mm
Dome diameter	53 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm

# AGILA TWIN

2970UOO050P30-11

EAN 4031582302769  
Order number 00030048



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

