

# LEVINA

5377PIP150P30-11 7001/3000

EAN 4031582363777  
Order number 00062832



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Levina
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	190 mm
Overall width	59 mm
Overall weight	0.705 kg

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	150 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	80 Shore A

## HOUSING

Material	Polyamide
Fork shape	Slim
Swivel bearing	Two ball races
Colour	Silver grey (RAL7001)
Offset	38 mm
Swivel radius	120 mm
Swivel interference	240 mm
Dome diameter	59 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm



Universal  
Design  
Award



Deutscher  
Designer  
Club

PRODUCT INFORMATION

# LEVINA

5377PIP150P30-11 7001/3000


EAN 4031582363777  
Order number 00062832



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---



Universal  
Design  
Award



Deutscher  
Designer  
Club