

AGILA TWIN

2970UOO050P40 (12)

EAN 4031582458138



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ●
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	154.32 lb
Electric conductive	no
Stainless	no
Load capacity Static	308.65 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	2.72 in
Overall weight	0.47 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	0.98 in
Swivel radius	2.09 in
Swivel interference	4.17 in

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.79 in
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Square plate
Plate length	2.36 in
Plate width	2.36 in
Plate hole length (Minimum)	1.5 in
Plate hole length (Maximum)	1.89 in
Plate hole width (Minimum)	1.5 in
Plate hole width (Maximum)	1.89 in
Plate hole diameter	0.25 in

AGILA TWIN

2970UOO050P40 (12)

EAN 4031582458138



BETTER MOBILITY. BETTER LIFE.

Product Drawings

