

KAPPA LOAD

9652ITP250P63 flat kick pedal

EAN 4031582445305



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Kappa load
Type	Swivel caster with total lock, head end of caster
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2204.62 lb
Electric conductive	no
Stainless	no
Load capacity Static	4409.24 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	12.01 in

HOUSING

Housing Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	2.4 in
Swivel radius	7.36 in
Swivel interference	14.72 in
Lubrication nipple	1

WHEEL

Tread profile	flat
Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	9.84 in
Tread width	2.17 in
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	5.31 in
Plate width	4.33 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

KAPPA LOAD

9652ITP250P63 flat kick pedal

EAN 4031582445305



BETTER MOBILITY. BETTER LIFE.

Product Drawings

