

KAPPA

9688FTP100P63 CL67

EAN 4031582316094
Order number 00801353



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Kappa
Type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	540 kg
Load capacity at 6 km/h	450 kg
Load capacity Static	900 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	145 mm
Overall width	98 mm
Overall weight	3.388 kg

WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	100 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Colour	Blue passivated
Lubrication nipple	✓
Dome diameter	96 mm

FITTING

Fitting type	Medium rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

KAPPA

9688FTP100P63 CL67

EAN 4031582316094
Order number 00801353



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

