

AVIANA

5976PIP075R36-32S1X30° N SO

EAN 4031582550368



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Aviana
Type	Swivel castor with central , total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	4.11 in
Overall width	2.72 in
Overall weight	1.59 lb

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Tread color	Anthracite gray (RAL7016)
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	2.95 in
Body width	0.98 in
Hardness of tread (A)	80 Shore A

HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Color	Silver gray (RAL7001)
Offset	1.14 in
Swivel radius	2.74 in
Swivel interference	5.43 in

FITTING

Fitting type	Stem with cam hole for profile bars, short version
Bolt diameter	1.26 in
Bolt length	2.01 in
Bolt thread position	0.28 in
Bolt mounting holes quantity	2



Red Dot
Design
Award



German
Design
Award