

# LUMINA

A520YGI050B10-11X20 DOM45

EAN 4031582341751



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Lumina
Housing type	Swivel castor
Electric conductive	✓
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.4 in
Overall width	2.17 in
Overall weight	0.23 lb

## WHEEL

Body material	Polypropylene, electric conductive
Tread material	Thermoplastic rubber, electric-conductive
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.31 in
Hardness of tread (A)	87 Shore A

## HOUSING

Material	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Swivel radius	2.01 in
Swivel interference	4.02 in
Dome diameter	1.77 in

## FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in

PRODUCT INFORMATION

# LUMINA

A520YGI050B10-11X20 DOM45

EAN 4031582341751



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

