

STORA

2875QMP125P72 TFR

EAN 4031582389814



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stora
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	60 °C
Overall height	160 mm
Overall weight	0.925 kg

WHEEL

Body material	Polyurethane injected
Tread material	Double flanged with tracks
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (D)	59 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Special Function
Swivel bearing	Two ball races
Offset	40 mm
Swivel interference	172 mm
Thread diameter	58.5 mm

FITTING

Fitting type	Vertical flange
Fitting height	63 mm
Plate length	35 mm
Plate width	10 mm

ADDITIONAL INFORMATION

Designed for the following palletsize: track width: approx. 2,75 mm, groove width: approx. 5,7 mm, groove depth: > 10 mm.

PRODUCT INFORMATION

STORA

2875QMP125P72 TFR

EAN 4031582389814



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

