

AGILA

2478PJP050P41

EAN 4031582327434



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad

FITTING

Fitting type	Square plate
Plate length	55 mm
Plate width	55 mm
Plate hole length (Minimum)	38.5 mm
Plate hole length (Maximum)	44 mm
Plate hole width (Minimum)	38.5 mm
Plate hole width (Maximum)	44 mm
Plate hole diameter	6.3 mm

CORE ATTRIBUTES

Product name	Agila
Housing type	Fixed castor
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	69 mm
Overall weight	0.095 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	50 mm
Tread width	19 mm
Hardness of tread (A)	87 Shore A

AGILA

2478PJP050P41

EAN 4031582327434



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

