

# FOOTMASTER

FOOT MASTER GDN- 80-S-NYN

EAN 4031582413175



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

## CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	500 kg
Electric Conductive	No
Stainless	No
Load capacity Static	500 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	102 mm
Overall width	86 mm
Overall weight	2 kg

## HOUSING

Housing Color	White
Offset	46 mm
Swivel radius	77.5 mm
Swivel interference	155 mm
Dome diameter	86 mm

## WHEEL

Bearing	Roller bearing, damped
Wheel Color	Black
Diameter	63 mm
Tread width	30 mm
Body width	30 mm

## FITTING

Bolt hole diameter	12 mm
--------------------	-------

# FOOTMASTER

FOOT MASTER GDN- 80-S-NYN

EAN 4031582413175

Order number 00062079  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

