

# LINEA LIGHT

5925UOI035P41-38x38/10 LOW

EAN 4031582409871



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product Name                | Linea light                    |
| Type                        | Swivel castor with wheel brake |
| Standard                    | EN12528 - Furniture Castors    |
| Load capacity at 3 km/h     | 50 kg                          |
| Electric Conductive         | No                             |
| Stainless                   | No                             |
| Load capacity Static        | 100 kg                         |
| Temperature range (Minimum) | -20 °C                         |
| Temperature range (Maximum) | 60 °C                          |
| Overall Height              | 48 mm                          |
| Overall width               | 52 mm                          |
| Overall weight              | 0.05 kg                        |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Housing Material    | Polyamide          |
| Fork shape          | Twin wheel housing |
| Swivel Bearing      | Stem, swiveling    |
| Offset              | 12 mm              |
| Swivel radius       | 45 mm              |
| Swivel interference | 90 mm              |

## WHEEL

|                    |                                |
|--------------------|--------------------------------|
| Body material      | Polyamide                      |
| Tread Material Mix | Identical with wheel body      |
| Bearing            | Plain bearing with spacer tube |
| Threadguards       | Without threadguard            |
| Diameter           | 35 mm                          |
| Tread width        | 11 mm                          |

## FITTING

|                             |              |
|-----------------------------|--------------|
| Fitting type                | Square plate |
| Plate length                | 38 mm        |
| Plate width                 | 38 mm        |
| Plate hole length (Maximum) | 27 mm        |
| Plate hole width (Maximum)  | 27 mm        |
| Plate hole diameter         | 5 mm         |



Deutscher  
Designer  
Club



Interzum  
Award



product  
design  
award

IF Design  
Award