

# AGILA

2470PJO100P50

EAN 4031582010428



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product Name	Agila
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Electric Conductive	No
Stainless	No
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	135 mm
Overall width	60 mm
Overall weight	0.57 kg

## HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	38 mm
Swivel radius	88 mm
Swivel interference	176 mm
Dome diameter	60 mm

## WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	87 Shore A

## FITTING

Fitting type	Rectangular plate
Plate length	77 mm
Plate width	67 mm
Plate hole length (Minimum)	46.5 mm
Plate hole length (Maximum)	51.5 mm
Plate hole width (Minimum)	56 mm
Plate hole width (Maximum)	61.5 mm
Plate hole diameter	8.5 mm

# AGILA

2470PJO100P50

EAN 4031582010428

Order number 00005163  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

