

# AGILA

2478PJH150P50

EAN 4031582439380



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Agila                     |
| Housing type                | Fixed castor              |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 100 kg                    |
| Load capacity Static        | 200 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall height              | 185 mm                    |
| Overall weight              | 0.662 kg                  |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread material        | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | With threadguard     |
| Diameter              | 150 mm               |
| Tread width           | 32 mm                |
| Hardness of tread (A) | 87 Shore A           |

## HOUSING

|               |                     |
|---------------|---------------------|
| Material fork | Steel sheet, medium |
| Fork shape    | Broad               |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 77 mm             |
| Plate width                 | 67 mm             |
| Plate hole length (Minimum) | 56 mm             |
| Plate hole length (Maximum) | 61.5 mm           |
| Plate hole width (Minimum)  | 46.5 mm           |
| Plate hole width (Maximum)  | 51.5 mm           |
| Plate hole diameter         | 8.5 mm            |

# AGILA

2478PJH150P50

EAN 4031582439380



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

