

# FOOTMASTER

FOOT MASTER GDN- 40-F-NYN

EAN 4031582413120



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

## CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	50 kg
Electric Conductive	No
Stainless	No
Load capacity Static	50 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	71 mm
Overall width	57 mm
Overall weight	0.32 kg

## HOUSING

Housing Color	White
Offset	30 mm
Swivel radius	51 mm
Swivel interference	102 mm
Dome diameter	57 mm

## WHEEL

Bearing	Roller bearing, damped
Wheel Color	Black
Diameter	42 mm
Tread width	19 mm
Body width	19 mm

## FITTING

Plate length	55 mm
Plate width	55 mm
Plate hole length (Maximum)	42 mm
Plate hole width (Maximum)	42 mm
Plate hole diameter	6.5 mm

# FOOTMASTER

FOOT MASTER GDN- 40-F-NYN

EAN 4031582413120

Order number 00062074  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

