

# FOOTMASTER

FOOT MASTER GDN- 60-F-NYN antistatic



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## CORE ATTRIBUTES

|                             |               |
|-----------------------------|---------------|
| Product Name                | Footmaster    |
| Type                        | Swivel castor |
| Load capacity at 3 km/h     | 125 kg        |
| Electric Conductive         | No            |
| Stainless                   | No            |
| Load capacity Static        | 250 kg        |
| Temperature range (Minimum) | -10 °C        |
| Temperature range (Maximum) | 90 °C         |
| Overall Height              | 82.5 mm       |
| Overall width               | 70 mm         |
| Overall weight              | 0.7 kg        |

## HOUSING

|                     |        |
|---------------------|--------|
| Offset              | 36 mm  |
| Swivel radius       | 63 mm  |
| Swivel interference | 126 mm |
| Dome diameter       | 70 mm  |

## WHEEL

|                    |                        |
|--------------------|------------------------|
| Body material      | Polyamide, super heavy |
| Tread Material Mix | Polyurethane, injected |
| Bearing            | Roller bearing, damped |
| Threadguards       | Without threadguard    |
| Diameter           | 50 mm                  |
| Tread width        | 25 mm                  |
| Body width         | 25 mm                  |

## FITTING

|                             |       |
|-----------------------------|-------|
| Plate length                | 73 mm |
| Plate width                 | 73 mm |
| Plate hole length (Maximum) | 58 mm |
| Plate hole width (Maximum)  | 58 mm |
| Plate hole diameter         | 7 mm  |

# FOOTMASTER

FOOT MASTER GDN- 60-F-NYN antistatic



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

