

LUMINA

AA25YGI050B10 11X20P

EAN 4031582404425



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric conductive	✓
Load capacity Static	80 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	58 mm
Overall width	55 mm
Overall weight	0.11 kg

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Thermoplastic rubber, electric-conductive
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Tread width	10 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Polypropylene
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Swivel radius	63 mm
Swivel interference	126 mm

FITTING

Fitting type	Stem with grip ring, with collar
Bolt hole diameter	10 mm
Stem diameter	11 mm