

# GALEA

5070PJP125R05-22X40 7035/7042/7035/7035

EAN 4031582308853



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion Resistance	● ● ● ● ○ ○

## CORE ATTRIBUTES

Product Name	Galea
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	162 mm
Overall width	65 mm
Overall weight	0.62 kg

## HOUSING

Housing Material	Polyamide
Fork shape	Closed
Swivel Bearing	Two ball races
Housing Color	Light grey (RAL7035)
Offset	40 mm
Swivel radius	95 mm
Swivel interference	190 mm
Dome diameter	59 mm

## WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Precision ball bearing
Tread Color	Traffic grey A (RAL7042)
Wheel Color	Traffic grey A (RAL7042)
Threadguards	With threadguard
Diameter	125 mm
Tread width	30 mm
Axle Hole Diameter	0 mm
Hub Length	0 mm
Body width	30 mm
Hardness of tread (A)	90 Shore A

## FITTING

Fitting type	Solid stem, round
Bolt diameter	22 mm
Bolt length	40 mm

# GALEA

5070PJP125R05-22X40 7035/7042/7035/7035

EAN 4031582308853

Order number 00073989  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

