

INTEGRAL

2040XSX200R05-32

EAN 4031582341782



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------------------|
| Product name | Integral |
| Type | Swivel castor |
| Standard | similar EN12531- Hospital Bed Castors |
| Load capacity at 1.8 mph | 330.69 lb |
| Load capacity at 2.5 mph | 330.69 lb |
| Electric conductive | ✓ |
| Load capacity Static | 661.39 lb |
| Temperature range (Minimum) | -22 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 9.02 in |
| Overall weight | 3.81 lb |
| Certification | Tested and monitored by TÜV Süd |

WHEEL

| | |
|-----------------------|---|
| Body material | Polyamide, electric conductive |
| Tread material | Polyurethane, injected, electric-conductive |
| Bearing | Precision ball bearing, sealed |
| Threadguards | Integrated threadguard |
| Diameter | 7.87 in |
| Tread width | 1.38 in |
| Hardness of tread (D) | 59 Shore D |

HOUSING

| | |
|---------------------|------------------------|
| Material | Steel sheet, medium |
| Fork shape | Closed |
| Swivel bearing | Precision ball bearing |
| Offset | 2.36 in |
| Swivel radius | 6.3 in |
| Swivel interference | 12.6 in |

FITTING

| | |
|---------------|--|
| Fitting type | Solid stem, round |
| Bolt diameter | 1.26 in |
| Bolt length | 1.77 in |
| Hint | Washable beds must be sealed in the fitting area by the hospital bed manufacturer. |

ADDITIONAL INFORMATION

Washable according AK-BWA



IF Design Award



Red Dot Design Award

INTEGRAL




2040XSX200R05-32

EAN 4031582341782



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



IF
Design
Award



Red Dot
Design
Award