

# AGILA

2470PNP125P30

EAN 4031582421910



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Load capacity Static	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	160 mm
Overall weight	0.701 kg

## WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (A)	70 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	41 mm
Swivel radius	103.5 mm
Swivel interference	207 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm
Hint	Castors can be mounted with standard screws of any length.

# AGILA

2470PNP125P30

EAN 4031582421910



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

