

LEVINA

5370JP100P50 7001

EAN 4031582347463



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Levina
CO2 emission (scope 3)	2.01
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	137 mm
Overall width	59 mm
Overall weight	0.47 kg

HOUSING

Housing Material	Polyamide
Fork shape	Slim
Swivel Bearing	Two ball races
Housing Color	Silver grey (RAL7001)
Offset	36 mm
Swivel radius	86 mm
Swivel interference	172 mm
Dome diameter	59 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Precision ball bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	77 mm
Plate width	67 mm
Plate hole length (Minimum)	46.5 mm
Plate hole length (Maximum)	51.5 mm
Plate hole width (Minimum)	56 mm
Plate hole width (Maximum)	61.5 mm
Plate hole diameter	8.5 mm



Universal
Design
Award



Deutscher
Designer
Club

LEVINA

5370PJP100P50 7001





EAN 4031582347463

Order number 00035830

Product Drawings



BETTER MOBILITY. BETTER LIFE.



Universal
Design
Award



Deutscher
Designer
Club