

# AGILA

2475PJI050P30-11 SCREWED

EAN 4031582050059  
Order number 00003896



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	69 mm
Overall width	43 mm
Overall weight	0.159 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	19 mm
Body width	19 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	24 mm
Swivel radius	82 mm
Swivel interference	164 mm
Dome diameter	41 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm
Hint	Castors can be mounted with standard screws of any length.

# AGILA

2475PJI050P30-11 SCREWED

EAN 4031582050059  
Order number 00003896



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

