

# AGILA

2470PIO150P30-13

EAN 4031582365054



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Agila                     |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 80 kg                     |
| Electric conductive         | ✓                         |
| Load capacity Static        | 160 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall height              | 185 mm                    |
| Overall weight              | 0.764 kg                  |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Tread material        | Solid rubber, non-marking |
| Bearing               | Plain bearing             |
| Threadguards          | Without threadguard       |
| Diameter              | 150 mm                    |
| Tread width           | 32 mm                     |
| Hardness of tread (A) | 80 Shore A                |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Offset              | 45 mm               |
| Swivel radius       | 120 mm              |
| Swivel interference | 240 mm              |

## FITTING

|                    |  |
|--------------------|--|
| Fitting type       | Bolt hole  |
| Bolt hole diameter | 13 mm  |
| Hint               | Castors can be mounted with standard screws of any length. |

PRODUCT INFORMATION

# AGILA

2470PIO150P30-13

EAN 4031582365054



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

