

ULTRATECH

FCP 160x50-Ø20 HL60



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Ultratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1763.7 lb
Load capacity at 3.7 mph	1410.96 lb
Electric conductive	no
Stainless	no
Load capacity Static	3527.39 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	5.65 lb

WHEEL

Body material	Casting
Tread material	Ultratech Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Sapphire blue (RAL5003)
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

ULTRATECH

FCP 160x50-Ø20 HL60




BETTER MOBILITY. BETTER LIFE.

Product Drawings



ULTRATECH

FCP 160x50-Ø20 HL60



BETTER MOBILITY. BETTER LIFE.