

AGILA TWIN

2976UAE075P54

EAN 4031582302882



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila twin
Housing type	Swivel castor with central, total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	103 mm
Overall weight	0.67 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Cone ball bearing, stainless
Diameter	75 mm
Tread width	25 mm
Hardness of tread (D)	42 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	28 mm
Swivel radius	65.5 mm
Swivel interference	131 mm

FITTING

Fitting type	Rectangular plate with brake elements
Plate length	70 mm
Plate width	55 mm
Plate hole length (Minimum)	51 mm
Plate hole length (Maximum)	57 mm
Plate hole width (Maximum)	41 mm
Plate hole diameter	5.5 mm

AGILA TWIN

2976UAE075P54

EAN 4031582302882



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

