

SCOUT

814SUF200P60 180° SMART

EAN 4031582429916



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Scout
Type	Swivel castor with spring loaded directional lock
Load capacity at 3 km/h	150 kg
Load capacity at 4 km/h	150 kg
Stainless	✓
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	242 mm
Overall width	72 mm
Overall weight	2.912 kg

WHEEL

Body material	Polyamide
Tread hardness	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	200 mm
Tread width	40 mm
Hardness of tread (A)	64 Shore A

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Angular
Swivel bearing	Precision ball bearing
Offset	50 mm
Swivel radius	150 mm
Swivel interference	300 mm

FITTING

Fitting type	Rectangular plate
Plate length	130 mm
Plate width	74 mm
Plate hole length (Maximum)	110 mm
Plate hole width (Maximum)	50 mm
Plate hole diameter	10.5 mm

SCOUT

814SUF200P60 180° SMART

EAN 4031582429916



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

