

AGILA TWIN

2970PIP075P30-10

EAN 4031582362282



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	99 mm
Overall weight	0.541 kg

WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Hardness of tread (A)	75 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	31.4 mm
Swivel radius	68.9 mm
Swivel interference	137.8 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	10 mm

AGILA TWIN

2970PIP075P30-10

EAN 4031582362282



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

