

# AGILA TWIN

2970PJP050P30-11 VERVALLEN

EAN 4031582429510



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila twin
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	154.32 lb
Load capacity Static	308.65 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	2.72 in
Overall weight	0.69 lb

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	1.97 in
Tread width	0.75 in
Hardness of tread (A)	80 Shore A

## HOUSING

Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	0.98 in
Swivel radius	2.09 in
Swivel interference	4.17 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in

# AGILA TWIN

2970PJP050P30-11 VERVALLEN

EAN 4031582429510



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

