

# AGILA TWIN

2977PJO050P40 TFR

EAN 4031582386448



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Agila twin                    |
| Type                        | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 70 kg                         |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 140 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall Height              | 69 mm                         |
| Overall weight              | 0.3 kg                        |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Twin wheel housing  |
| Swivel Bearing      | Two ball races      |
| Offset              | 25 mm               |
| Swivel radius       | 99 mm               |
| Swivel interference | 198 mm              |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread Material Mix    | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | Without threadguard  |
| Diameter              | 50 mm                |
| Tread width           | 19 mm                |
| Hardness of tread (A) | 87 Shore A           |

## FITTING

|                             |              |
|-----------------------------|--------------|
| Fitting type                | Square plate |
| Plate length                | 60 mm        |
| Plate width                 | 60 mm        |
| Plate hole length (Minimum) | 38 mm        |
| Plate hole length (Maximum) | 48 mm        |
| Plate hole width (Minimum)  | 38 mm        |
| Plate hole width (Maximum)  | 48 mm        |
| Plate hole diameter         | 6.3 mm       |

# AGILA TWIN

2977PJO050P40 TFR

EAN 4031582386448



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

