

# AGILA

2475DYK050P30-11

EAN 4031582344318



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product Name	Agila
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	Yes
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall Height	69 mm
Overall width	43 mm
Overall weight	0.22 kg

## HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	24 mm
Swivel radius	82 mm
Swivel interference	164 mm
Dome diameter	41 mm

## WHEEL

Body material	Sheet Steel
Tread Material Mix	Solid rubber, black, electric-conductive
Bearing	Cone ball bearing
Wheel Color	Blue passivated
Threadguards	With threadguard
Diameter	50 mm
Tread width	19 mm
Body width	19 mm
Hardness of tread (A)	80 Shore A

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm
Hint	Castors can be mounted with standard screws of any length.

# AGILA

2475DYK050P30-11

EAN 4031582344318

Order number 00005489  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

