

LUMINA

A520POI035P41-38X38/8

EAN 4031582409895



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product name | Lumina |
| Type | Swivel castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 30 kg |
| Load capacity Static | 60 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 49 mm |
| Overall width | 38 mm |
| Overall weight | 0.02 kg |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polypropylene |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 35 mm |
| Tread width | 6 mm |
| Hardness of tread (D) | 65 Shore D |

HOUSING

| | |
|---------------------|---------------------------------------|
| Material fork | Polypropylene |
| Fork shape | Twin wheel housing, closed, with dome |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 33.5 mm |
| Swivel interference | 67 mm |

FITTING

| | |
|-----------------------------|--------------|
| Fitting type | Square plate |
| Plate length | 38 mm |
| Plate width | 38 mm |
| Plate hole length (Maximum) | 27 mm |
| Plate hole width (Maximum) | 27 mm |
| Plate hole diameter | 5 mm |